



NOTES :

- A: Model name, input voltage range, nominal output voltage, maximum output current, country of manufacture and safety marking (C-UL-US, DEMKO & CE marking) are shown here in accordance with the specifications.
- B: M3 tapped holes 4 for customer chassis mounting (FG).
- C: Input and output terminal : 8- ϕ 2
- D: Signal pin : 8- ϕ 1
- E: Unless otherwise specified dimensional tolerance : ± 0.3

(unit : mm)

MODEL NAME	PAF600F24-*
TDK-Lambda	
C169-02-01/6-E	