



NOTES :

- A: Model name, input voltage range, nominal output voltage, maximum output current, country of manufacture and safety marking (For only approved products) are shown here in accordance with the specifications.
- B: M3 tapped holes 4 for customer chassis mounting (FG).
- C: Input and Output pin : 8- ϕ 2
- D: Signal pin : 8- ϕ 1
- E: Unless otherwise specified dimensional tolerance : ± 0.3 mm

(unit : mm)

MODEL NAME	PAF600F280-*
TDK-Lambda	
C176-02-01E	