



CONNECTORS USED:

| PART DESCRIPTION | PART NAME | MANUFACT. | QTY |
|-------------------------------|-----------|-----------|-----|
| PIN HEADER (INPUT SIDE CN1) | B3P5-VH | J.S.T. | 1 |
| PIN HEADER (OUTPUT SIDE CN51) | B8P-VH | J.S.T. | 1 |

*OUTPUT CURRENT OF EACH CONNECTOR PIN MUST BE LESS THAN 5A.

MATCHING HOUSINGS, PINS & TOOL (NOT INCLUDED WITH THE PRODUCT):

| PART DESCRIPTION | PART NAME | MANUFACT. | QTY |
|-----------------------|--------------|-----------|-----|
| SOCKET HOUSING (CN1) | VHR-5N | J.S.T. | 1 |
| SOCKET HOUSING (CN51) | VHR-8N | J.S.T. | 1 |
| TERMINAL PINS | SVH-21T-P1.1 | J.S.T. | 11 |
| | BVH-21T-P1.1 | | |
| HAND CRIMPING TOOL | YC-160R | J.S.T. | - |

NOTES

A: M4 EMBOSSED TAPPED & COUNTERSINK HOLES (6) ARE FOR CUSTOMER'S CHASSIS MOUNTING.

B: Ø4.5 HOLES (3) AND R2.25 SLOT HOLES (2) ARE FOR CUSTOMER'S CHASSIS MOUNTING.

C: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.

D: \perp IS PROTECTIVE BONDING TERMINAL.

(unit : mm)

| | |
|------------|-------------|
| MODEL NAME | ZWS100BAF/A |
|------------|-------------|

TDK-Lambda

A249-02-01/A-C