



SEE NOTE A

NAME PLATE



SEE NOTE B



NOTES

- A: MODEL NAME, MAXIMUM OUTPUT POWER, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- B: COUNTRY OF MANUFACTURE WILL BE SHOWN HERE.
- C: RECOMMENDED SCREW TORQUE(M2.5~M2.6 SCREW): 0.56N·m (5.0Lb·inch).
- D: RECOMMENDED WIRE: AWG12~24, WIRE STRIP LENGTH: 4~5mm, 5mm Max.

(unit : mm)

MODEL NAME	DRL60-1
<b>TDK-Lambda</b>	

CA818-02-01