



NAME PLATE SEE NOTE A

DRB240-24-1 TDK-Lambda

Input Details  
100-240VAC 2.7A  
Frequency: 50 / 60Hz

Output Details  
DC 24-28V/10-8.6A  
Maximum power: 240W

Caution: For use in a controlled environment, refer to manual for conditions.  
Attention: Pour une utilisation dans un environnement contrôlé, reportez-vous au manuel d'instructions pour les conditions.

RISK OF ELECTRIC SHOCK  
Read manual PA635-04-02\_ Further information at: [emea.tdk-lambda.com/PA635-04-01\\_](http://emea.tdk-lambda.com/PA635-04-01_)

25°C to 70°C  
Wiring must be ≥105°C rated  
Le câblage doit être ≥105°C nominale

QR CODE EHPF

IND. CONT. EQ. E483168

MADE IN CHINA

NOTE :  
A. MODEL NAME , INPUT VOLTAGE RANGE , NOMINAL OUTPUT VOLTAGE , MAXIMUM OUTPUT CURRENT & COUNTRY OF MANUFACTURE ARE SHOWN IN ACCORDANCE WITH THE SPECIFICATION.

(UNIT:mm)

MODEL	DRB240-24-1
<b>TDK-Lambda</b>	
PA635-02-01B	