



NOTES :

A: Model name, input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (C-UL-US & Demko marking) are shown here in accordance with the specifications.

B: Input, Output and signal terminals : 6- $\phi 1.0 \pm 0.1$

C: Unless otherwise specified dimensional tolerance :  $\pm 0.5$

(unit : mm)

MODEL NAME	CCG15-48-xxD/P
<b>TDK-Lambda</b>	

C283-02-01/P