



NOTES :

A: Model name, input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (C-UL-US & Demko marking) are shown here in accordance with the specifications.

B: Input, Output and signal terminals : 6- $\phi$ 1.0 $\pm$ 0.1

C: Unless otherwise specified dimensional tolerance :  $\pm$ 0.5

(unit : mm)

MODEL NAME	CCG30-48-xxS
<b>TDK-Lambda</b>	

C267-02-01B