

CONNECTORS USED

PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
PIN HEADER (INPUT SIDE CN1)	B3P5-VH	JST	1
PIN HEADER(OUTPUT SIDE CN51)	B6P-VH	JST	1

* OUTPUT CURRENT OF EACH CONNECTOR PIN MUST BE LESS THAN 5A.

MATCHING HOUSINGS & PIN.

* NOT INCLUDED WITH THE PRODUCT.


SOCKET HOUSING (CN1)	VHR-5N	JST	1
SOCKET HOUSING (CN51)	VHR-6N	JST	1
TERMINAL PINS (CN1, CN51)	SVH-21T-P1.1	JST	9

HAND CRIMPING TOOL: YC-160R

MANUFACTURER: JST

NAME PLATE

SEE NOTE B



SEE NOTE C

NOTES:

- A.THE 4- ϕ 3.5 HOLES ARE CUSTOMER'S CHASSIS MOUNTING HOLES. ALL MUST BE SCREWED IN ORDER TO CONFORM THE VIBRATION SPEC.
- B.MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- C.COUNTRY OF MANUFACTURE WILL BE SHOWN HERE.
- D.TO KEEP THE DISTANCE MORE THAN 4m/m BETWEEN PC-BOARD EDGE AND CUSTOMER'S CHASSIS.
- E.FG IS FOR SAFETY GROUND CONNECTION.

(unit : mm)

MODEL NAME	CME150
DENSEI-LAMBDA	

B019-02-01D