



NOTES :

- A: Model name, input voltage range, nominal output voltage, maximum output current, country of manufacture and safety marking (C-UL-US, DEMKO & CE marking) are shown here in accordance with the specifications.
- B: M3 tapped holes 4 for customer chassis mounting (FG).
- C: Output terminals : 2- ϕ 2.0
- D: Input and signal terminals : 7- ϕ 1
- E: Unless otherwise specified dimensional tolerance : \pm 0.25
- F: 5V output model : NC
12V, 15V, 24V output models : PC

(unit : mm)

MODEL NAME	CN200A110
TDK-Lambda	
C257-02-01B	