



NOTES :

- A: Model name, input voltage range, nominal output voltage, maximum output current, country of manufacture and safety marking (C-UL-US, DEMKO & CE marking) are shown here in accordance with the specifications.
- B: M3 tapped holes 2 for customer chassis mounting (FG).
- C: Output terminals : 2- $\phi 1.5$
- D: Input and signal terminals : 6- $\phi 1$

(unit : mm)

MODEL NAME	CN30A110/CO
TDK-Lambda	
C256-02-01/30C0-A	