



NOTES :

- A: Model name, input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (C-UL-US, DEMKO, TUV & CE marking) are shown here in accordance with the specifications.
- B: $\varnothing 3.3$ holes 4 for customer chassis mounting (FG).
- C: Output terminals : 4- $\varnothing 2$
- D: Input and signal terminals : 6- $\varnothing 1$
- E: Unless otherwise specified dimensional tolerance : ± 0.25

(unit : mm)

MODEL NAME	PH600A280/T
TDK-Lambda	

C285-02-01/T