


NOTES

- A : M4 TAPPED HOLES
12 POINTS FOR CUSTOMER CHASSIS MOUNTING.
SCREWS MUST NOT BE PROTRUDE INTO POWER SUPPLY BY 7mm.
 - B : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE,
AND MAXIMUM OUTPUT CURRENT ARE SHOWN HERE
IN ACCORDANCE WITH THE SPECIFICATIONS.
 - C : COUNTRY OF MANUFACTURE WILL BE SHOWN HERE.
 - D: IS PROTECTIVE BONDING TERMINAL.
- TOLERANCE : ±1mm UNLESS OTHERWISE SPECIFIED.

ACCESSORIES

- * SHORT PIECE (NET 2) FOR SHORTING PURPOSE
(+S~+V, -S~-V) : MOUNTED AT TIME OF SHIPMENT.
- * TERMINAL COVER 1 (NET 1)
(MOUNTED AT TIME OF SHIPMENT)
- * TERMINAL COVER 2 (NET 1)
(MOUNTED AT TIME OF SHIPMENT)



(unit : mm)

MODEL NAME	RDS180A-24
TDK-Lambda	
A283-02-01	