



- NOTES:
- A: M3 EMBOSSED TAPPED HOLES(6) ARE FOR CUSTOMER CHASSIS MOUNTING. SCREWS MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 4mm.
 - B: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, AND NOMINAL OUTPUT CURRENT ARE ON NAME PLATE IN ACCORDANCE WITH THE SPECIFICATIONS.
 - C: COUNTRY OF MANUFACTURE WILL BE SHOWN HERE.
 - D. RECOMMENDED WIRE = SOLID AND STRANDED AWG12-20 (0.5-3.5mm²)
 - E. RECOMMENDED SCREW TORQUE = 1.27N·m

(unit : mm)

MODEL	DLP180-24-1
DENSEI-LAMBDA	
CA735-02-01J	