



- NOTES:
- A: M3 EMBOSSED TAPPED HOLES(6) ARE FOR CUSTOMER CHASSIS MOUNTING. SCREWS MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 4mm.
  - B: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, AND NOMINAL OUTPUT CURRENT ARE ON NAME PLATE IN ACCORDANCE WITH THE SPECIFICATIONS.
  - C: COUNTRY OF MANUFACTURE WILL BE SHOWN HERE.
  - D: RECOMMENDED WIRE = SOLID AND STRANDED AWG12-20 ( 0.5-3.5mm<sup>2</sup> )  
WIRE STRIP LENGTH = 6-7mm
  - E: RECOMMENDED SCREW TORQUE = 0.49N·m

(unit : mm)

MODEL NAME	DLP240-24-1/EJ
<b>TDK-Lambda</b>	
CA736-02-01/EJ-G	