



NOTES :

- A : M3 EMBOSSED TAPPED & COUNTERSUNK HOLES (3) ARE FOR CUSTOMER CHASSIS MOUNTING. SCREWS MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 4mm.
- B : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE AND NOMINAL OUTPUT CURRENT ARE ON NAME PLATE IN ACCORDANCE WITH THE SPECIFICATIONS.
- C : COUNTRY OF MANUFACTURE WILL BE SHOWN HERE.
- D : RECOMMENDED WIRE = SOLID AND STRANDED AWG12-20 (0.5-3.5mm²) WIRE STRIP LENGTH = 6-7mm
- E : RECOMMENDED SCREW TORQUE = 0.49N·m

(unit : mm)

MODEL NAME	DLP75-24-1/EJ
TDK-Lambda	

CA733-02-01/EJ-F