



NOTES :

- A: Model name, input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (C-UL-US, TÜV & CE marking) are shown here in accordance with the specifications.
- B: M3 tapped holes 4 for customer chassis mounting (FG).
- C: Output terminal : 2- ϕ 2
- D: Input, Intermediate terminal and signal pin : 9- ϕ 1
- E: Unless otherwise specified dimensional tolerance : ± 0.3

(unit : mm)

MODEL NAME	PFE300SA
TDK-Lambda	

C274-02-01A