



NOTES :

- A: Model name, input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (C-UL-US, SEMKO & CE marking) are shown here in accordance with the specifications.
- B: M3 tapped holes 4 for customer chassis mounting (FG).
- C: Output terminal : 2- ϕ 2
- D: Input and Intermediate terminal : 5- ϕ 1
- E: Signal pin (+S, -S, TRIM, ENA, IOG, AUX, +ON/OFF, -ON/OFF, PC, COM) : 10- \square 0.64
- F: Unless otherwise specified dimensional tolerance : \pm 0.3

(unit : mm)

MODEL NAME	PFE500F
DENSEI-LAMBDA	

C250-02-01C