



NOTES :

- A: Model name, input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (C-UL-US, TÜV & CE marking) are shown here in accordance with the specifications.
- B: M3 tapped holes 4 for customer chassis mounting (FG).
- C: Output terminal : 2-Ø2
- D: Input, Intermediate terminal and signal pin : 9-Ø1
- E: Unless otherwise specified dimensional tolerance : ±0.3

(unit : mm)

MODEL NAME	PFE500SA
TDK-Lambda	

C265-02-01B