



NOTES :

- A: Model name, input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (C-UL-US, TÜV & CE marking) are shown here in accordance with the specifications.
- B: M3 tapped holes 4 for customer chassis mounting (FG).
- C: Output terminal : 2- $\phi$ 2
- D: Input, Intermediate terminal and signal pin : 9- $\phi$ 1
- E: Unless otherwise specified dimensional tolerance :  $\pm 0.3$

(unit : mm)

MODEL NAME	PFE700SA
<b>TDK-Lambda</b>	

C275-02-01