



NOTES :

- A: Model name, input voltage range, nominal output voltage, maximum output current, country of manufacture and safety marking (C-UL-US, DEMKO & CE marking) are shown here in accordance with the specifications.
- B: M3 tapped holes 2 for customer chassis mounting (FG).
- C: Output pin : 2- ϕ 1.5
- D: Input and Signal pin : 6- ϕ 1.0
- E: Unless otherwise specified dimensional tolerance : \pm 0.25mm

(unit : mm)

MODEL NAME	PH100A280
TDK-Lambda	
C271-02-01A	