



NOTES :

- A: Model name, input voltage range, nominal output voltage, maximum output current, country of manufacture and safety marking (C-UL-US, DEMKO & CE marking) are shown here in accordance with the specifications.
- B: M3 tapped holes 2 for customer chassis mounting (FG).
- C: Output pin : 2- $\phi 1.5$
- D: Input and Signal pin : 6- $\phi 1.0$
- E: Unless otherwise specified dimensional tolerance :  $\pm 0.25$ mm

(unit : mm)

MODEL NAME	PH150A280
<b>TDK-Lambda</b>	
C263-02-01E	