



NOTES :

- A: Model name, input voltage range, Nominal output voltage, Maximum output current, country of manufacture and safety marking (C-UL-US, DEMKO, TÜV & CE marking) are shown here in accordance with the specifications.
- B:  $\varnothing 3.3$  holes 4 for customer chassis mounting (FG).
- C: Output terminals : 4- $\varnothing 2$
- D: Input and signal terminals : 6- $\varnothing 1$
- E: Unless otherwise specified dimensional tolerance :  $\pm 0.25$

(unit : mm)

MODEL NAME	PH300A280/T
<b>TDK-Lambda</b>	

CA836-02-01/T-B