


AIR FLOW 





== NOTES ==

A : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT AND COUNTRY OF MANUFACTURE ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.

NAME PLATE DETAILS

RWS300B-5

RWS300B-12,15,24,28,36,48



SCALE FOR NAME PLATE : 2/1

B : 4-M3 BR & COUNTERSINK ARE FOR CUSTOMER'S CHASSIS MOUNTING. (SCREW PENETRATION DEPTH 6mm MAX.)

(unit : mm)

MODEL NAME	RWS300B
TDK-Lambda	
A261-02-01F	