



ACCESSORIES

ITEM	PART NUMBER	QTY	PACKING	OUTER PACKING	NOTE
BUS BAR PROTECTION	IA702-33-16_	1		PLASTIC BAG	
BUS BAR PROTECTION	IA702-33-17_	1			
PT SCREW KA40x8	STAINLESS STEEL	2	PLASTIC BAG		
CONNECTORS PROTECTION	IA702-33-04_	1			
CABLE HOUSING SAMTEC	IPD1-06-D-K	1		PLASTIC BAG	
CONTACT PINS SAMTEC	CC79R-2024-01-L	12	PLASTIC BAG	PLASTIC BAG	
CABLE HOUSING SAMTEC	IPD1-02-D-K	1		PLASTIC BAG	
CONTACT PINS SAMTEC	CC79R-2024-01-L	6	PLASTIC BAG	PLASTIC BAG	
CABLE HOUSING SAMTEC	IPD1-04-D-K	1		PLASTIC BAG	
CONTACT PINS SAMTEC	CC79R-2024-01-L	8	PLASTIC BAG		
LINKING CABLE	IA575-81-11_	1	PLASTIC BAG		

- NOTE
1. MOUNTING SCREWS MUST NOT PROTRUDE INTO THE POWER SUPPLY MORE THAN 6.0 mm. TIGHTENING TORQUE MUST BE MAX. 0.58 Nm
 2. RS232/RS485 COMMUNICATION RJ-45, SHIELDED, 8 CONTACTS CONNECTORS.
 3. MODEL NAME AND OUTPUT RATING SHOWN HERE ACCORDING TO THE SPECIFICATION.
 4. M6 OR 1/4 " SCREWS FOR LOAD WIRES CONNECTION.
 5. INPUT VOLTAGE AND CURRENT RATING ARE SHOWN HERE ACCORDING TO THE SPECIFICATION.
 6. AC INPUT RATING, SAFETY APPROVAL AND EU LABEL.

7. RECEPTACLE SAMTEC P/N IPD1-06-D-K
CONTACT PIN SAMTEC CC79R-2024-01-L
HAND TOOL: CAT-HT-179-2024-11 WIRE AWG 20-24.
8. RECEPTACLE SAMTEC P/N IPD1-04-D-K
CONTACT PIN SAMTEC CC79R-2024-01-L
HAND TOOL: CAT-HT-179-2024-11 WIRE AWG 20-24.
9. FUSE HOLDER FOR MODELS:
400W 10V
600W 10V~20V
800W 10V~36V

(unit : mm)

MODEL NAME	Z-SERIES BINDING POST OPTION
TDK-Lambda	
IA702-02-03H	