



NOTE

1. MOUNTING SCREWS MUST NOT PROTRUDE INTO THE POWER SUPPLY MORE THAN 6mm.
2. EXTERNAL CONTROL CONNECTOR;  
CONNECTOR: AMP, P/N 102617-5  
RECEPTACLE: AMP, P/N 87631-9  
RECEPTACLE CONTACTS: AMP, P/N 87523-5(STRIIP FORM)  
P/N 87523-6(LOOSE PIECE)  
WIRE AWG: 24 TO 20  
HAND TOOL FOR WIRES CONNECTION: AMP, P/N 90202-2
3. RS232/RS485 COMMUNICATION  
TIA/EIA-568A, SHIELDED, 8 CONTACTS CONNECTORS.
4. MODEL NAME AND OUTPUT RATING SHOWN HERE ACCORDING TO THE SPECIFICATION.
5. INPUT VOLTAGE AND CURRENT RATING ARE SHOWN HERE ACCORDING TO THE SPECIFICATIONS
6. SAFETY AND EU REPRESENTATIVE ADDRESS LABEL.

(unit : mm)

MODEL NAME	ZUP HI-VOLTAGE
<b>TDK-Lambda</b>	
IA572-02-01B	