



CONNECTOR USED :

PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
PIN HEADER (OUTPUT SIDE CN3)	B2B-XH-A	JST	1

RECOMMENDED HOUSING & TERMINAL PIN :

* NOT INCLUDED WITH THE PRODUCT.

PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
SOCKET HOUSING (CN3)*1	XHP-2	JST	1
TERMINAL PINS (CN3)*1	BXH-001T-P0.6 OR SXH-001T-P0.6	JST	2

HAND CRIMPING TOOL : YC-110R OR YRS-110 CN3 MANUFACTURER : JST

*1 APPLICABLE ONLY WHEN USING REMOTE ON/OFF

== NAME PLATE ==

ZWD225PAF-0524/T

INPUT : 100-240VAC~3.0A
50/60Hz

OUTPUT: 5V --- 5.0A
24V --- 9.0A

RATED POWER : 225W
24V : 14/18A PEAK @ 100/200VAC

MADE IN CHINA

TDK-Lambda

BAUART GEPRÜFT
TYPE APPROVED

Tüv Rheinland Product Safety

SEE NOTE C

SEE NOTE B

== NOTE ==

- A. THE 5-ø3.5 HOLES ARE FOR CUSTOMER'S CHASSIS MOUNTING HOLE. ALL MUST BE SCREWED IN ORDER TO CONFORM THE VIBRATION SPEC.
- B. MODEL NAME, INPUT VOLTAGE RANGE, AVERAGE OUTPUT POWER, NOMINAL OUTPUT VOLTAGE, AVERAGE OUTPUT CURRENT AND PEAK OUTPUT CURRENT ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- C. COUNTRY OF MANUFACTURER WILL BE SHOWN HERE.
- D. TO KEEP A DISTANCE MORE THAN 4.5mm FROM PC-BOARD EDGE, LEAD CUT AND COMPONENT HEIGHT TO CUSTOMER'S CHASSIS.
- E. FG IS FOR SAFETY GROUND CONNECTION.
- F. CN3 IS NORMALLY SHORTED BY JM-2W-96(JST). IF USING REMOTE ON/OFF, REMOVE JM-2W-96 AND REFER TO THE TABLE FOR RECOMMENDED HOUSING AND TERMINAL PIN.

(unit : mm)

MODEL NAME	ZWD225PAF/T
TDK-Lambda	

PA574-02-01/T-E