

| Model Number | Switching Frequency(kHZ) | |
|--------------|--------------------------|--------|
| | 115Vac | 230Vac |
| DPP15-24 | 60 | 70 |
| DPP25-5 | 60 | 90 |
| DPP30-12 | 90 | 150 |
| DPP30-24 | 75 | 130 |
| DPP50-15 | 65 | 105 |
| DPP50-24 | 55 | 95 |
| DPP50-48 | 55 | 95 |
| DPP100-24 | 55 | 55 |
| DPP120-12-1 | 55 | 55 |
| DPP120-24-1 | 50 | 50 |
| DPP120-48-1 | 55 | 55 |
| DPP240-24-1 | 40 | 40 |
| DPP240-48-1 | 40 | 40 |
| DPP480-24-1 | 65 | 65 |
| DPP480-48-1 | 65 | 65 |
| DSP10-05 | 55 | 65 |
| DSP10-12 | 75 | 95 |
| DSP10-15 | 80 | 100 |
| DSP10-24 | 95 | 80 |
| DSP30-05 | 30 | 30 |
| DSP30-12 | 35 | 35 |
| DSP30-15 | 45 | 45 |
| DSP30-24 | 35 | 35 |
| DSP60-05 | 40 | 40 |
| DSP60-12 | 30 | 30 |
| DSP60-15 | 55 | 55 |
| DSP60-24 | 45 | 45 |
| DSP100-05 | 40 | 40 |
| DSP100-12 | 30 | 30 |
| DSP100-15 | 50 | 50 |
| DSP100-24 | 45 | 45 |
| DSP100-24/C2 | 35 | 35 |