

Update on June 07, 2010

MODEL NO.	Vin : 115Vac (typ.)	Vin : 230Vac (typ.)
DPP15-24	1.15W	2.05W
DPP25-5	1.0W	1.7W
DPP30-12	1.1W	1.8W
DPP30-24	1.2W	2.2W
DPP50-15	1.4W	2.4W
DPP50-24	1.3W	2.4W
DPP50-48	1.2W	2.3W
DPP100-24	2.5W	3.0W
DPP120-12-1	2.4W	3.1W
DPP120-24-1	2.8W	3.3W
DPP120-48-1	4.0W	4.7W
DPP240-24-1	3.5W	4.0W
DPP240-48-1	3.8W	4.3W
DPP480-24-1	2.7W	3.8W
DPP480-48-1	3.0W	4.1W
DSP10-5	0.37W	0.62W
DSP10-12	0.52W	0.72W
DSP10-15	0.75W	1.15W
DSP10-24	0.68W	0.95W
DSP30-5	0.9W	2.1W
DSP30-12	1.0W	2.0W
DSP30-15	1.1W	2.0W
DSP30-24	1.2W	2.4W
DSP60-5	1.0W	1.8W
DSP60-12	1.0W	1.9W
DSP60-15	1.1W	2.1W
DSP60-24	1.4W	2.6W
DSP100-5	0.9W	1.9W
DSP100-12	1.2W	2.5W
DSP100-15	1.2W	3.4W
DSP100-24	1.3W	3.2W
MODEL NO.	Vin : 400Vac (typ.)	Vin : 500Vac (typ.)
DPP120-12-3	3.5W	4.6W
DPP120-24-3	3.5W	5.7W
DPP240-24-3	4.1W	4.5W
DPP240-48-3	4.2W	5.5W
DPP480-24-3	13.2W	17.2W
DPP480-48-3	15.2W	19.0W
DPP960-24-3	36.0W	46.6W
DPP960-48-3	43.1W	57.2W