

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power supply

Name and address of the applicant

TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195
JAPAN

Name and address of the manufacturer

TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195
JAPAN

Name and address of the factory

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR
BARU JAYA GADING 26070 KUANTAN PAHANG
MALAYSIA

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

- 1) LWT15H-5FF
- 2) LWT15H-522
- 3) LWT15H-525
- 4) LWT15H-522/TSK

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014/ A11:2017.
National Differences specified in the CB Test Report. Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E122103-A6045-CB-1 issued on 2020-01-27

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2020-01-28

Signature:

For full legal entity names see www.ul.com/ncbnames

Masamichi Takagi



Ref. Certif. No.

JP-21486-UL

Factories:

TDK-LAMBDA (CHINA) ELECTRONICS CO LTD
NO 6 XING CHUANG ER LU WUXI JIANGSU 214028
CHINA

ZHANGJIAGANG HUA YANG ELECTRONICS CO LTD
NO.15 TONGXIN RD, ZHAOFENG ECONOMIC DEVELOPMENT ZONE, LEYU TOWN ZHANGJIAGANG JIANGSU
215622
CHINA

Ratings:

Input

100-240 VAC, 0.6 A, 50/60 Hz

Output:

1) LWT15H-5FF

5 VDC, 3 A, +15 VDC, 0.6 A, -15 VDC, 0.4 A

2) LWT15H-522

5 VDC, 3 A, +12 VDC, 0.6 A, -12 VDC, 0.4 A

3) LWT15H-525

5 VDC, 3 A, +12 VDC, 0.6 A, -5 VDC, 0.4 A

4) LWT15H-522/TSK

5 VDC, 1 A, +12 VDC, 0.1 A, -12 VDC, 0.1 A

Total Output Power: 17 W

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2020-01-28

Signature:

Masamichi Takagi