

# FA23C0G2E154JRU06




## Application

Automotive Grade

## Series

FA23



## Dimensions

L	8.5mm Max.
W	11mm Max.
T	5.5mm Max.
F	5mm +0.8,-0.2mm
d	0.5mm +0.1,-0.03mm

## Temperature Characteristic

-55 to 125°C 0+/-30ppm/°C

## Rated Voltage

250Vdc

## Capacitance

150nF

## Capacitance Tolerance

J (+/-5%)

## Q Factor





1000 Min.

## Insulation Resistance

3.333Gohm Min

## AEC-Q200

Yes



Characterization Sheet (MLCC with Dipped Radial Lead)



All specifications are subject to change without notice.

July 27, 2018