

# FA24NP02W332JNU06




## Application

Automotive Grade

## Series

FA24



## Dimensions

L	
W	5.5mm Max.
T	3mm Max.
F	5mm +/-1mm
d	0.5mm +0.1,-0.03mm

## Temperature Characteristic

-55 to 150°C 0+/-30ppm/°C

## Rated Voltage

450Vdc

## Capacitance

3.3nF

## Capacitance Tolerance

+/-5%

## Q Factor





1000 Min

## Insulation Resistance

10000Mohm Min.

## AEC-Q200

YES



Characterization Sheet (MLCC with Dipped Radial Lead)



All specifications are subject to change without notice.

March 8, 2016