

FA26NP02E223JNU00




Application

Automotive Grade

Series

FA26



Dimensions

L	7mm+/-2mm
W	6mm Max.
T	3.5mm Max.
F	5mm +/-1mm
d	0.5mm +0.1,-0.03mm
l	7mm+/-2mm

Temperature Characteristic

-55 to 150°C 0+/-30ppm/°C

Rated Voltage

250Vdc

Capacitance

22nF

Capacitance Tolerance

+/-5%

Q Factor





1000 Min

Insulation Resistance

10000Mohm Min.

AEC-Q200

YES



Characterization Sheet (MLCC with Dipped Radial Lead)



All specifications are subject to change without notice.

March 8, 2016