

Application

Automotive Grade

Series

FA28



Dimensions

- L 4mm Max.
- W 5.5mm Max.
- T 2.5mm Max.
- F 5mm +/-1mm
- d 0.5mm +0.1,-0.03mm
- l 7mm +/-2mm

Temperature Characteristic

-55 to 125°C 0+/-30ppm/°C

Rated Voltage

50Vdc

Capacitance

3.3nF

Capacitance Tolerance

+/-5%

Q Factor

1000 Min.

Insulation Resistance

10000Mohm Min.

AEC-Q200

Yes

