

# FA28NP02E122JNU00




## Application

Automotive Grade

## Series

FA28



## Dimensions

L	7mm+/-2mm
W	5.5mm Max.
T	2.5mm Max.
F	5mm +/-1mm
d	0.5mm +0.1,-0.03mm
l	7mm+/-2mm

## Temperature Characteristic

-55 to 150°C 0+/-30ppm/°C

## Rated Voltage

250Vdc

## Capacitance

1.2nF

## Capacitance Tolerance

+/-5%

## Q Factor





1000 Min

## Insulation Resistance

10000Mohm Min.

## AEC-Q200

YES



Characterization Sheet (MLCC with Dipped Radial Lead)



All specifications are subject to change without notice.

March 8, 2016