

CKG32KC0G2A683J335AJ

TDK Item Description : CKG32KC0G2A683JT****




Application & Main Feature

Automotive Grade (MEGACAP Type)

Series

CKG32K(3225) [EIA 1210]



Dimensions

L	3.60mm +/-0.3mm
W	2.60mm +/-0.3mm
T	3.35mm +/-0.1mm
E	0.80mm +/-0.15mm

Temperature Characteristic

C0G (-55 to 125 degC 0+/-30ppm/degC)

Rated Voltage

2A (100Vdc)

Capacitance

68nF

Capacitance Tolerance

J (+/-5%)

Q Factor

1000 Min.

Insulation Resistance

7.352Gohm Min

AEC-Q200

Yes

