


# Licence for



## CENELEC ENEC Agreement Licence Ref. No. SE/07115-1G

<b>Product:</b>	<b>Filter unit for radio interference suppression</b>
<b>Type designation:</b>	RSEL-20****, RSAL-20****
<b>Test Report No.</b>	1720151STO-001
<b>Licence holder:</b>	TDK Corporation Electronic Components Business Company Magnetics Business Group 1-11, Kabayachi, Kisakata-Machi Nikaho-shi, Akita-ken 018-0146 JAPAN
<b>The product complies with the standard(s):</b>	EN 60939-1:2010 EN 60939-2:2005
<b>Licence holder is authorized to use the mark with the following limitations:</b>	-
<b>Date of expiry:</b>	31 December 2022

### Additional information in Appendix

<i>Certification Body</i>	Intertek Semko AB, Product Certification	<i>Place</i>	Kista - Stockholm
<i>Signed</i>	 Bo Berglöf	<i>Date</i>	6 March 2018
<i>Internal reference:</i>	SMS		<i>Page 1 of 3</i>

This Licence is the result of testing a sample of the product submitted, in accordance with the provisions of the relevant specific standard. A copy of the Licence shall be filed in the place of manufacturing. The Licence has been established by a body which is a signatory to the ENEC Agreement ratified by CENELEC Marks Committee on 10 April 1992.

## APPENDIX

### CENELEC ENEC Agreement Licence Ref. No. SE/07115-1G

Test Report No. 1720151STO-001

#### Technical data

Type designation	RSEL-20****
Rated voltage	250VAC
Frequency	50/60Hz
Rated current	0.5, 1, 2, 3, 6A
Capacitance	2 x 0.1uF X2 + 0 or 2 x 3300pF Y2
Inductance	2 x 16.4, 12.3, 7.3, 4.4, 0.89mH
Rated temperature	55°
Climatic category	25/100/21
Trade mark	TDK-Lambda

Type designation	RSAL-20****
Rated voltage	250VAC
Frequency	50/60Hz
Rated current	0.5, 1, 2, 3, 6A
Capacitance	2 x 0.1uF X2 + 0 or 2 x 3300pF Y2
Inductance	2 x 10.5, 7.9, 4.7, 2.8, 0.57mH
Rated temperature	55°
Climatic category	25/100/21
Trade mark	TDK-Lambda

Capacitors included shall be certified according to the standard EN/IEC 60384-14:2013.

#### Alternative design:

RSEL-20R5	0.5A	2x16.4mH
RSEL-2001	1A	2x12.3mH
RSEL-2002	2A	2x7.3mH
RSEL-2003	3A	2x4.4mH
RSEL-2006	6A	2x0.89mH

RSAL-20R5	0.5A	2x10.5mH
RSAL-2001	1A	2x7.9mH
RSAL-2002	2A	2x4.7mH
RSAL-2003	3A	2x2.8mH
RSAL-2006	6A	2x0.57mH

## APPENDIX

### CENELEC ENEC Agreement Licence Ref. No. SE/07115-1G

RS\*L-20\*\*\*\*: W = insulated wire, AWG 20  
A = flat connector, 2.8x0.5mm

RS\*L-20\*\*\*\*: No letter = with 2x3300pF Y-capacitors  
L = without Y-capacitors

**Manufacturing site(s):** Guangxi Wuzhou City Pingzhou  
Electronics Co., Ltd.  
No. 81, Yong An Road, Longxu Town  
Longxu District, Wuzhou City  
Guangxi Province, 543100  
CHINA

This certificate replaces previously issued ref. No. SE/07115-1F dated 2 May 2013.  
A new certificate has been issued on account of expired valid date.

*Certification Body* Intertek Semko AB, Product Certification *Place* Kista - Stockholm

*Signed*

  
Bo Berglöv

*Date* 6 March 2018