



NOTE:

- A :  $\varnothing 3.5$  HOLES FOR CUSTOMER CHASSIS MOUNTING.
- B : M3 TAPPED & EMBOSSED HOLES FOR CUSTOMER CHASSIS MOUNTING.
- C :  $\varnothing 3.5$  HOLES FOR CUSTOMER CHASSIS MOUNTING.
- D : M3 TAPPED & STANDOFF HOLES FOR FG CONNECTION.
- E : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT AND COUNTRY OF MANUFACTURE ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.

CONNECTORS USED:

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
PIN HEADER (INPUT SIDE CN1)	B2P3-VH(LF)(SN)	J.S.T	1
PIN HEADER (OUTPUT SIDE CN51)	B4P-VH(LF)(SN)	J.S.T	1

MATCHING HOUSINGS, PINS & TOOL (NOT INCLUDED WITH THE PRODUCT):

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
SOCKET HOUSING(CN1)	VAR-2/VHR-3N	J.S.T	1
SOCKET HOUSING(CN51)	VHR-4N	J.S.T	1
TERMINAL PINS	SVH-41T-P1.1	J.S.T	6
	BVH-41T-P1.1		
HAND CRIMPING TOOL	YC-930R	J.S.T	-
	YC-931R		

(unit : mm)

MODEL NAME	CUS75EB/A
------------	-----------

**TDK-Lambda**

CA833-02-01/75EBA-A