



CONNECTORS USED:

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
PIN HEADER (INPUT SIDE CN1)	TL402V-0754-03P-G12S	TIANLI	1
PIN HEADER (OUTPUT SIDE CN51)	TL100V-0755-05P-G12S	TIANLI	1

\*OUTPUT CURRENT OF EACH CONNECTOR PIN MUST BE LESS THAN 5A.

NOTES :

- A: 4- $\phi$ 3.5 HOLES ARE CUSTOMER'S CHASSIS MOUNTING HOLES AND INSERT SPACER (MAX  $\phi$ 6.2) OF HEIGHT OVER 8mm TO LIFT THE UNIT. ALL MUST BE SCREWED AND GROUNDED.
- B: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, NOMINAL OUTPUT CURRENT, PEAK OUTPUT CURRENT AND SAFETY MARKING(FOR ONLY APPROVED PRODUCTS)ARE SHOWN ON THE NAME PLATE IN ACCORDANCE WITH THE SPECIFICATIONS. COUNTRY OF MANUFACTURE WILL BE SHOWN ON THE NAME PLATE.
- C:  $\perp$  IS FOR SAFETY GROUND CONNECTION.
- D: TO KEEP THE DISTANCE MORE THAN 4mm BETWEEN PC-BOARD EDGE AND CUSTOMER'S CHASSIS.

(unit : mm)

MODEL NAME	CUT35J/T
<b>TDK-Lambda</b>	

CA873-02-01/T-A