



CONNECTORS USED:

PART DESCRIPTION	PART NAME	MANUFACT.	QTY
PIN HEADER (INPUT SIDE CN1)	TL402V-0754-03P-G12S	TIANLI	1
PIN HEADER(OUTPUT SIDE CN51)	TL100V-0755-08P-G12S	TIANLI	1

*OUTPUT CURRENT OF EACH CONNECTOR PIN MUST BE LESS THAN 5A.

NOTES

- A: THE 2-M3 TAPPED & STANDOFF FOR CUSTOMER CHASSIS MOUNTING.SCREWS MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 5mm.
- B: THE 2-M4 EMBOSSED TAPPED & COUNTER-SUNK HOLES FOR CUSTOMER CHASSIS MOUNTING. SCREWS MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 8mm.
- C: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, NOMINAL OUTPUT CURRENT, PEAK OUTPUT CURRENT AND SAFETY MARKING(FOR ONLY APPROVED PRODUCTS)ARE SHOWN ON THE NAME PLATE IN ACCORDANCE WITH THE SPECIFICATIONS. COUNTRY OF MANUFACTURE WILL BE SHOWN ON THE NAME PLATE.
- D: \perp IS FOR SAFETY GROUND CONNECTION.

(unit : mm)

MODEL NAME	CUT75/TA
TDK-Lambda	

CA809-02-01/TA-B