



**NOTES**

- A. MODEL NAME , INPUT VOLTAGE RANGE , NOMINAL OUTPUT VOLTAGE , MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATION.
- B. RECOMMENDED SCREW TORQUE M3: 4.4-5.9KGF.CM.
- C. RECOMMENDED WIRE: AWG14-20, WIRE STRIP LENGTH: 8MM.

(unit : mm)

|                   |             |
|-------------------|-------------|
| MODEL NAME        | DRB120-24-1 |
| <b>TDK-Lambda</b> |             |
| PA634-02-01G      |             |