



== NOTES ==

- A : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- B : RECOMMENDED SCREW TORQUE(M3.5): 1.0-1.4N.m(10.2-14.2kgf.cm).
- C : RECOMMENDED WIRE: AWG16-20.

(unit : mm)

MODEL NAME	DRJ100/C2
TDK-Lambda	
A268-02-01/C2-A	