



== NOTES ==

- A : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- B : RECOMMENDED WIRE: AWG14-20, WIRE STRIP LENGTH: 8mm.

(unit : mm)

MODEL NAME	DRJ100/E
TDK-Lambda	
A268-02-01/E-B	