



NOTES

- A. MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- B. RECOMMENDED WIRE: AWG14-20, WIRE STRIP LENGTH: 8-10MM.

(unit : mm)

MODEL NAME	DRJ120-24-1/E
TDK-Lambda	
PA637-02-01/E-J	