



== NOTES ==

A : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.

B : RECOMMENDED WIRE: AWG14-20, WIRE STRIP LENGTH: 8mm.

(unit : mm)

MODEL NAME	DRJ15/E
TDK-Lambda	

A265-02-01/E-C