



== NOTES ==

A : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.

B : RECOMMENDED SCREW TORQUE: INPUT/OUTPUT TERMINAL 1.0N.m(10.2kgf.cm).  
 ⊕ TERMINAL 1.0N.m(10.2kgf.cm).

C : RECOMMENDED WIRE: AWG16-20.

(unit : mm)

MODEL NAME	DRJ15
<b>TDK-Lambda</b>	

A265-02-01C