



NOTES

- A. MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- B. RECOMMENDED SCREW TORQUE M3.5: 1.0-1.6NM (10.2-16.3KGF.CM).
- C. RECOMMENDED WIRE: AWG14-20.

(unit : mm)

MODEL NAME	DRJ240-24-1
TDK-Lambda	

PA638-02-01G