



== NOTES ==

A : MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.

B : RECOMMENDED SCREW TORQUE(M3.5): 1.0-1.4N.m(10.2-14.2kgf.cm).

C : RECOMMENDED WIRE: AWG16-20.

(unit : mm)

MODEL NAME	DRJ50
TDK-Lambda	
A267-02-01C	