




[1571#14AWG 1C+1(14AWG)]  
SECTIONAL DRAWING




4P POWER DIN  
FRONT VIEW





S.R: AD-A7 SERIES

SECTION A-A



[包裝方式]

TITLE		DC CORD 1050mm 1C+1(4P POWER DIN)				DESCRIPTION				COMPONENT LIST		REVISIONS	
MODEL		A7 Medical 12V~24V 全系列 TDK-Lambda				MATERIAL				1.CABLE : COLOR BLACK UL/CSA 1571 80/90°C 30V 14AWGX1C+ DRAIN WIRE(14AWG)		Rev.A 新版發行 (R1091) 2010/06/10	
DWG NO.		EG-MAP-02-850E		UNIT	mm	THICKNESS				2.PVC WIRES : WHITE		Rev.B 修改線材耐電壓為30V 2011/01/04	
PART NO.		P54400D0740E		SCALE		FINISH				3.CONNECTOR : 年永4PIN POWER DIN OR EQ		Rev.C 修正線材敘述錯誤 2011/02/17	
PREPARE	DRAWING	CHECKED	APPROVED	REV.	E	TOLERANCE				4.末端剝7.0mm鍍錫		Rev.D 取消PCB端子 2012/03/07	
	Sam			DATE	2014/01/28	 		5.對應測試頭: 4PIN POWER DIN (FEMALE) MDP-002-4PIN (P530600004F0001)		Rev.E 變更腳位 2014/01/28			