




[2464#16AWG 3C+1(16AWG)]
SECTIONAL DRAWING



SECTION A-A

[包裝方式]

TITLE						DC CORD 1000mm 3C+1(4P POWER DIN)		DESCRIPTION		COMPONENT LIST		REVISIONS			
MODEL		AD-A8 Medical 全系列				TDK-Lambda		MATERIAL		1.CABLE : COLOR BLACK UL/CSA 2464 80/90°C 300V 16AWGX3C+DRAIN WIRE+ALUMINUM SHIELD 2.PVC WIRES : RED/YELLOW/BLACK 3.CONNECTOR : 4PIN POWER DIN 4.末端剥10全鍍錫. 5.對應測試頭 : 4PIN POWER DIN (FEMALE) MDP-002-4PIN (P530600004F0001)		Rev.A 新版發行		2012/02/06	
DWG NO.		EG-MAP-02-968A		UNIT		mm		THICKNESS							
PART NO.		P54400D0848A				SCALE		FINISH							
PREPARE		DRAWING		CHECKED		APPROVED		TOLERANCE							
		呂芳凱													
				REV.		A									
				DATE		2012/02/06									