


1 2 3 4

A

B

C



J1

PIN	CONNECTION
1	NEUTRAL
2	NOT CONNECTED
3	LIVE
4	NOT CONNECTED
5	EARTH

J2
TOP ROW: 0V PINS 6 - 10
BOTTOM ROW: +V PINS 1 - 5

J3 FAN DRIVE (OPEN FRAME/'U' CHANNEL ONLY) *

PIN	CONNECTION
1	0V
2	+V
3	TEMP CONTROL

* NOTE:FOR (J) MODEL FACTORY USE ONLY

MATING PARTS

CONNECTOR	HOUSING	CRIMP PIN	MANUFACTURER
J1	VHR-5N	SVH-21T-P1.1	JST
J2	39-01-2105	44476-3112	MOLEX
J3	02201-3037	08-50-0032	MOLEX

D

NOTE:
A 4 OFF HOLES Ø3.5mm CLEARANCE FOR M3 FIXINGS.
ALL TOLERANCES +/-0.5mm.

E

REV.	MOD	DATE
01	DESIGN	09/10/2009
02	44652	07/12/2009


REVISIONS

This drawing and any information or descriptive matter contained therein are the confidential and copyright property of TDK-Lambda UK Limited. Neither the whole nor any extract may be disclosed, loaned, copied or used for manufacturing or tendering purpose without their written consent. ©

F

MATERIAL SPECIFICATION N/A	TDK-Lambda TDK-Lambda UK Limited. http://www.uk.tdk-lambda.com	TITLE EFE300 (J) OUTLINE DRAWINGS (OPEN FRAME)	SHEET 1/2
FINISH SPECIFICATION N/A		DRAWING NUMBER 60905	DRAWN BY P.H. DATE 09.10.09
COMMENTS General Tolerances Refer to 67960		PROJECT EFE300	SCALE 1:2 DO NOT SCALE

This drawing is SolidWorks produced.
All changes must be effected through the CAD System.
Drawn to BS8888.



UNLESS OTHERWISE STATED, DIMS IN mm.

A4